

MagniFlex™

Quick Start Guide



WHAT'S INCLUDED

- (1) MagniFlex
- (1) Microfiber Cloth
- (1) Microfiber Storage Pouch
- (4) CR2016 Coin Batteries
- (1) 30" Type-C to USB Charging Cable



*(2) of the CR2016 Coin Batteries will come installed in the MagniFlex.

COMPONENTS

1. Lens
2. Flexible Joints
3. LED Light Power Button
4. LED Light
5. Type-C Port (Input)
6. Coin Battery Door
7. Coin Battery Slot



TECH SPECS

Model: LIM-MGFX-XXX

Magnification: 2-4x

Light Source: 14 LED Lights

Type-C Input: Under 5V/1.5A

Battery Type: CR2016

Battery Run Time:

Low: 15 Hours

Medium: 12 Hours

High: 8 Hours

Material: Silicone + K9 Lens

Folded Size: 4.84" x 4.06" x 0.95"

Unfolded Size: 4.84" x 4.06" x 2.91"

Lens Diameter: 2.83"

Weight: 0.4 lb

USING THE MAGNIFIER

The flexible silicone material can expand and tilt to achieve different levels of magnification and view angles.

2x Magnified



3x Magnified



4x Magnified



3x Magnified



HOW TO USE

Powering the MagniFlex

There are two ways to power the MagniFlex in order to use the LED Light:

1. Using (2) of the included CR2016 Coin Batteries.

NOTE: Remove the Pull Tab before using.

2. Using the included Type-C to USB Cable. Connect the USB Cable to the MagniFlex and to a USB power source (not included).

NOTE: It is recommended to remove the CR2016 Coin Batteries when using the USB Cable as a power source.

Using the LED Lights

The LED Lights have three adjustable brightness levels. Single click the LED Light Power Button to turn the LED Light on and scan through the modes.

High | Medium | Low | Off

Changing the CR2016 Coin Batteries

1. Open the Coin Battery Door by pushing outwards against the arrow with light pressure and lifting upwards.
2. Install (2) of the CR2016 Coin Batteries in the Coin Battery Slot with the writing on the Coin facing upwards.

NOTE: The LED Light will not work if the CR2016 Coin Batteries are installed incorrectly.



SAFETY INFORMATION

By using the Limitless MagniFlex, you hereby agree that Limitless Innovations, Inc., an Illinois corporation and its affiliates (“Limitless”) shall have no liability for any losses associated with property damage, personal injury or loss of life that are incurred by you or by any third party in connection with or relating in any manner whatsoever to your use of the Limitless MagniFlex. By using the Limitless MagniFlex, you hereby agree at all times to comply fully with all safety warnings, operating instructions and general safety information in this user manual. By using the Limitless MagniFlex, you further agree to hold harmless Limitless, (and Limitless’ officers, directors, shareholders and employees) in connection with any losses sustained by you (including, without limitation, losses arising in whole or in part from property damage, personal injury or loss of life) relating in any manner whatsoever to your use of the Limitless MagniFlex.

WARNING

- Do **NOT** place the magnifying glass in direct sunlight. Reflection of direct sunlight by the glass could cause a fire.
- Wipe the lens with the included Microfiber Cloth to prevent scratching.
- Limitless MagniFlex is **NOT** a toy and should be kept away from children.
- **NEVER** use detergent, gasoline furniture polish, paint thinner, or other chemicals to clean any part of the magnifying glass, as it will damage the lens.
- Do **NOT** attempt to disassemble, repair, or open the Limitless MagniFlex or its accessories in any way.
- The MagniFlex is **NOT** waterproof and should **NEVER** be used in wet conditions.
- Batteries should be recycled or disposed of, as per state and local guidelines.

To view the complete user manual, please visit:
LimitlessInnovations.com/MagniFlex

LIMITLESS™

All rights reserved.
Limitless MagniFlex™, MagniFlex™, and Limitless™ are trademarks of Limitless Innovations, Inc. Design and specifications subject to change without notice. Products may vary from images shown.
Accessories sold separately.

LimitlessInnovations.com
Support@LimitlessInnovations.com
(855) 843-4828

Limitless Innovations, Inc.
4800 Metalmaster Way
McHenry, IL 60050

© Limitless Innovations, Inc.



@LimitlessInnovations



/LimitlessInnov



/LimitlessInnov



/LimitlessInnov



Limitless Innovations